

PRODUCT INFORMATION

# NOVATECH

RK.ETP085x80-Ø47x15,5

EAN 4031582369571



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Body material	Undefined
Tread Material Mix	Polypropylene, soft
Diameter	85 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	15.5 mm

### PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

Product Drawings

