

PRODUCT INFORMATION

SUPRATECH

PJP125x32-Ø8 TFR

EAN 4031582482676



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.28 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	36.5 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJP125x32-Ø8 TFR

EAN 4031582482676



BETTER MOBILITY. BETTER LIFE.

Product Drawings

