

# FOOTMASTER

FOOT MASTER GD-150-F-MCN

EAN 4031582413281



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ○ ○ ○ ○ ○ |
| Movement Noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion Resistance | ○ ○ ○ ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product Name                | Footmaster    |
| Type                        | Swivel castor |
| Load capacity at 3 km/h     | 1500 kg       |
| Electric Conductive         | No            |
| Stainless                   | No            |
| Load capacity Static        | 1500 kg       |
| Temperature range (Minimum) | -10 °C        |
| Temperature range (Maximum) | 90 °C         |
| Overall Height              | 132 mm        |
| Overall width               | 116 mm        |
| Overall weight              | 3.2 kg        |

## HOUSING

|                     |        |
|---------------------|--------|
| Housing Color       | White  |
| Offset              | 69 mm  |
| Swivel radius       | 117 mm |
| Swivel interference | 234 mm |
| Dome diameter       | 116 mm |

## WHEEL

|             |                        |
|-------------|------------------------|
| Bearing     | Roller bearing, damped |
| Wheel Color | Blue                   |
| Diameter    | 90 mm                  |
| Tread width | 56 mm                  |
| Body width  | 56 mm                  |

## FITTING

|                             |        |
|-----------------------------|--------|
| Plate length                | 100 mm |
| Plate width                 | 100 mm |
| Plate hole length (Maximum) | 70 mm  |
| Plate hole width (Maximum)  | 70 mm  |
| Plate hole diameter         | 13 mm  |

# FOOTMASTER

## FOOT MASTER GD-150-F-MCN

EAN 4031582413281

Order number 00062084  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

FOOT MASTER GD-150-F-MCN

