

FOOTMASTER

FOOT MASTER GD-150-F-MCN

EAN 4031582413281



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	1500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	132 mm
Overall width	116 mm
Overall weight	3.2 kg

HOUSING

Housing Color	White
Offset	69 mm
Swivel radius	117 mm
Swivel interference	234 mm
Dome diameter	116 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Blue
Diameter	90 mm
Tread width	56 mm
Body width	56 mm

FITTING

Plate length	100 mm
Plate width	100 mm
Plate hole length (Maximum)	70 mm
Plate hole width (Maximum)	70 mm
Plate hole diameter	13 mm

FOOTMASTER

FOOT MASTER GD-150-F-MCN

EAN 4031582413281

Order number 00062084
Product Drawings



BETTER MOBILITY. BETTER LIFE.

FOOT MASTER GD-150-F-MCN

