

DURATECH HEAT

BOG080X35-Ø11.1

EAN 4031582436723



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.18 kg

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Diameter	80 mm
Tread width	35 mm
Axle hole diameter	11.1 mm
Hub length	43.5 mm
Hardness of tread (D)	85 Shore D

DURATECH HEAT

BOG080X35-Ø11.1

EAN 4031582436723



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

