PRODUCT INFORMATION

DURATECH HEAT

WOO075x25-Ø8 HL26,5

EAN 4031582367355



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	200 °C

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	8 mm
Hub Length	26.5 mm


DURATECH HEAT

WOO075x25-Ø8 HL26,5

EAN 4031582367355

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH