

# ALPHA

3478DRJ100P62

EAN 4031582410679



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha                         |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 70 kg                         |
| Load capacity Static        | 140 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 128 mm                        |
| Overall weight              | 0.638 kg                      |

## WHEEL

|                       |   |
|-----------------------|---|
| Body material         | Sheet Steel                                   |
| Tread material        | Wound tread made of canvas and phenolic resin |
| Bearing               | Roller bearing                                |
| Axle                  | Screwed with nut                              |
| Threadguards          | With threadguard                              |
| Diameter              | 100 mm  |
| Tread width           | 30 mm   |
| Hardness of tread (A) | 85 Shore A                                    |

## HOUSING

|               |                    |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape    | Broad              |

## FITTING

|                             |                         |
|-----------------------------|-------------------------|
| Fitting type                | Small rectangular plate |
| Plate length                | 103 mm                  |
| Plate width                 | 85 mm                   |
| Plate hole length (Minimum) | 77 mm                   |
| Plate hole length (Maximum) | 80 mm                   |
| Plate hole width (Maximum)  | 60 mm                   |
| Plate hole diameter         | 9 mm                    |

# ALPHA

3478DRJ100P62

EAN 4031582410679



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

