

ELASTECH

IEP 100X40 HL49 ASM.

EAN 4031582319675
Broj porudžbine 00043125

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,515 kg

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
Boja Tocak	Metalni
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovina	8 mm
dužina glavnice	49 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

ELASTECH

IEP 100X40 HL49 ASM.

EAN 4031582319675
Broj porudžbine 00043125



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

