

# ALPHA

8499UFX160P67 Q1-11

EAN 4031582380774



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Movement noise ○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Load capacity at 3 km/h	300 kg
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	200 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall weight	1.992 kg

## WHEEL

Tread hardness	soft
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad

## FITTING

Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

# ALPHA

8499UFX160P67 Q1-11

EAN 4031582380774



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

