

# AGILA

R07-Ø31-35 INOX\_TBE

EAN 4031582437850



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Accessory
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.32 lb

## HOUSING

Stainless	✓
-----------	---

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	1.22 in
Expander fitting (Maximum)	1.38 in
Hint	Please indicate required tube innerdiameter when ordering.