

SUPRATECH

PJO050X18-Ø8

EAN 4031582428353



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.71 in
Axle hole diameter	0.31 in
Hub length	0.83 in
Hardness of tread (A)	87 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	77.16 lb
Load capacity Static	154.32 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.05 lb

SUPRATECH

PJO050X18-Ø8

EAN 4031582428353



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

