PRODUCT INFORMATION

AGILA

2477PIO150P30-11

EAN 4031582361940



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	185 mm
Overall weight	0.92 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	36 mm
Swivel radius	131 mm
Swivel interference	262 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, non-marking
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	150 mm
Tread width	30 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

© Copyright 2026 TENTE International GmbH


AGILA


2477PIO150P30-11

EAN 4031582361940

BETTER MOBILITY. BETTER LIFE.

Product Drawings





© Copyright 2026 TENTE International GmbH