

# NOVATECH

FTP200X80-Ø25 HL92

EAN 4031582419061



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | Ливено Гвожђе            |
| materijal omotaca          | Poliuretana, liveno      |
| Nošenje                    | precizini kuglicni lezaj |
| stitnici omotaca           | Sa threadguard           |
| Prečnik                    | 200 mm                   |
| Širina omotac              | 80 mm                    |
| dimenzija rupa osovina     | 25 mm                    |
| duzina glavčine            | 92 mm                    |
| Teškoća gazećeg omotac (A) | 92 Šor A                 |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                                  |
|--------------------------------|----------------------------------|
| Naziv proizvoda                | Novatech                         |
| Tip                            | Tocak                            |
| Standard                       | EN12533 - Tockoviza teske terete |
| Nosivost na 4 km/h             | 1680 kg                          |
| Nosivost na 6 km/h             | 1400 kg                          |
| Statički Nosivost              | 3360 kg                          |
| Temperaturni opseg (Minimalno) | -20 °C                           |
| Opseg temperature (maksimalni) | 60 °C                            |
| Ukupna težina                  | 7,056 kg                         |

# NOVATECH

FTP200X80-Ø25 HL92

EAN 4031582419061



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

