

## ZETA

4681ITP250P63 soft cv

EAN 4031582337655



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product Name                | Zeta                                |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12532 - Transport Equipment       |
| Load capacity at 4 km/h     | 800 kg                              |
| Load capacity at 6 km/h     | 640 kg                              |
| Electric Conductive         | No                                  |
| Stainless                   | No                                  |
| Load capacity Static        | 1600 kg                             |
| Temperature range (Minimum) | -10 °C                              |
| Temperature range (Maximum) | 60 °C                               |
| Overall Height              | 290 mm                              |
| Overall width               | 96 mm                               |
| Overall weight              | 4.6 kg                              |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Housing Material    | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel Bearing      | Two ball races, reinforced or stainless |
| Housing Color       | Blue passivated                         |
| Offset              | 55 mm                                   |
| Swivel radius       | 180 mm                                  |
| Swivel interference | 360 mm                                  |
| Dome diameter       | 96 mm                                   |

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Tread profile         | convex                   |
| Tread hardness        | soft                     |
| Body material         | Aluminium                |
| Tread Material Mix    | Polyurethane, casted     |
| Bearing               | Precision ball bearing   |
| Axle                  | Screwed with nut         |
| Wheel Color           | Traffic grey A (RAL7042) |
| Threadguards          | Without threadguard      |
| Diameter              | 250 mm                   |
| Tread width           | 50 mm                    |
| Body width            | 50 mm                    |
| Hardness of tread (A) | 80 Shore A               |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# ZETA

4681ITP250P63 soft cv

EAN 4031582337655

Order number 00838070

Product Drawings



BETTER MOBILITY. BETTER LIFE.

