

STYLEA

5923UJI065B10-11X20/10D23 9011/7016

EAN 4031582311006



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Stylea
Type	Swivel castor with intermittend brake
Standard	EN12529 - Swivel Chairs Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	No
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	68 mm
Overall width	43 mm
Overall weight	0.13 kg

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Housing Color	Graphite black (RAL9011)
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	23 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Anthracite grey (RAL7016)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	65 mm
Tread width	8 mm
Axle Hole Diameter	0 mm
Hub Length	0 mm
Body width	8 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

STYLEA

5923UJI065B10-11X20/10D23 9011/7016

EAN 4031582311006

Order number 00075210

Product Drawings



BETTER MOBILITY. BETTER LIFE.

