

NOVATECH

FTF230X82-Ø45-5XØ14

EAN 4031582331974



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|----------|
| Product name | Novatech |
| Type | Wheel |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 12.89 lb |

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Flanged wheel |
| Diameter | 9.06 in |
| Tread width | 3.23 in |
| Axle hole diameter | 1.77 in |
| Hardness of tread (A) | 92 Shore A |
| Hole circle diameter | 2.76 in |
| Fitting hole diameter | 0.55 in |
| Suitable for | jungheinrich_mic |

FITTING

| | |
|------------------------------|---|
| Bolt mounting holes quantity | 5 |
|------------------------------|---|

TECHNICAL DRAWINGS

