

PRODUCT INFORMATION

DURATECH

TOP082x88-Ø20 HL90

EAN 4031582322613



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Load capacity at 3 km/h	900 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.55 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	82 mm
Tread width	88 mm
Axle Hole Diameter	20 mm
Hub Length	90 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

DURATECH

TOP082x88-Ø20 HL90

EAN 4031582322613

Order number 00804433
Product Drawings



BETTER MOBILITY. BETTER LIFE.

