

AGILA

2470PJH075P40

EAN 4031582323757



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Swivel caster |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.94 in |
| Overall width | 1.69 in |
| Overall weight | 0.57 lb |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 0.94 in |
| Swivel radius | 2.42 in |
| Swivel interference | 4.84 in |
| Dome diameter | 1.69 in |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver gray (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 87 Shore A |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 2.36 in |
| Plate width | 2.36 in |
| Plate hole length (Minimum) | 1.5 in |
| Plate hole length (Maximum) | 1.89 in |
| Plate hole width (Minimum) | 1.5 in |
| Plate hole width (Maximum) | 1.89 in |
| Plate hole diameter | 0.25 in |

AGILA

2470PJH075P40

EAN 4031582323757

Order number 00003940
Product Drawings



BETTER MOBILITY. BETTER LIFE.

