

NOVATECH

ITP 100x50-Ø25

EAN 4031582319866



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1190.49 lb
Load capacity at 3.7 mph	947.99 lb
Electric conductive	no
Stainless	no
Load capacity Static	2380.99 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.31 lb




PRODUCT INFORMATION

NOVATECH

ITP 100x50-025

EAN 4031582319554

Order number 00830808



BETTER MOBILITY. BETTER LIFE.