

SUPRATECH

PJR100X32-Ø12 HL34,9

EAN 4031582320510
Order number 00030823



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Axle hole diameter	12 mm
Hub length	34.9 mm
Hardness of tread (A)	87 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.156 kg

SUPRATECH

PJR100X32-Ø12 HL34,9

EAN 4031582320510
Order number 00030823



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

