

ALPHA STAINLESS

8478UFX160P63

EAN 4031582313369
Order number 00035534



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall width	115 mm
Overall weight	1.846 kg

WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, sealed
Axle	Screwed with nut
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Colour	Stainless steel

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ALPHA STAINLESS

8478UFX160P63

EAN 4031582313369
Order number 00035534



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

