

PLATE

P10-40x20 / 8

EAN 4031582338102



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Stem with U-shaped plate
Plate length	40 mm
Plate width	20 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	4 mm

PERFORMANCE

Corrosion Resistance ●●●○○

CORE ATTRIBUTES

Product Name	Plate
Type	Accessory
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Overall Height	8 mm
Overall weight	0.03 kg