

PRODUCT INFORMATION

DURATECH

UOD200x50-Ø20 NL58

EAN 4031582439007



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	2.09 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing, stainless
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (D)	75 Shore D

DURATECH

UOD200x50-Ø20 NL58

EAN 4031582439007



BETTER MOBILITY. BETTER LIFE.

Product Drawings

