

# FOOTMASTER

FOOT MASTER GDN- 80-S-NYN

EAN 4031582413175



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ○ ○ ○ ○ ○ |
| Movement noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion resistance | ○ ○ ○ ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product name                | Footmaster    |
| Type                        | Swivel caster |
| Load capacity at 1.8 mph    | 1102.31 lb    |
| Electric conductive         | no            |
| Stainless                   | no            |
| Load capacity Static        | 1102.31 lb    |
| Temperature range (Minimum) | 14 °F         |
| Temperature range (Maximum) | 194 °F        |
| Overall height              | 4.02 in       |
| Overall width               | 3.39 in       |
| Overall weight              | 4.41 lb       |

## HOUSING

|                     |         |
|---------------------|---------|
| Housing Color       | White   |
| Offset              | 1.81 in |
| Swivel radius       | 3.05 in |
| Swivel interference | 6.1 in  |
| Dome diameter       | 3.39 in |

## WHEEL

|             |                        |
|-------------|------------------------|
| Bearing     | Roller bearing, damped |
| Wheel color | Black                  |
| Diameter    | 2.48 in                |
| Tread width | 1.18 in                |
| Body width  | 1.18 in                |

## FITTING

|                    |         |
|--------------------|---------|
| Bolt hole diameter | 0.47 in |
|--------------------|---------|

# FOOTMASTER

FOOT MASTER GDN- 80-S-NYN

EAN 4031582413175

Order number 00062079  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

