

## NOVATECH

FTP 300x100-Ø40 HL120

EAN 4031582319439



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK


|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | Ливено Гвожђе            |
| materijal omotaca          | Poliuretana, liveno      |
| Nošenje                    | precizini kuglicni lezaj |
| Boja Tocak                 | Med žuta (RAL1005)       |
| stitnici omotaca           | Sa threadguard           |
| Prečnik                    | 300 mm                   |
| Širina omotac              | 100 mm                   |
| dimenzija rupa osovina     | 40 mm                    |
| dužina glavnice            | 120 mm                   |
| Širina tela                | 100 mm                   |
| Teškoća gazećeg omotac (A) | 92 Šor A                 |
| Teškoća gazećeg omotac (D) | 42 Šor D                 |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                                   |
|--------------------------------|-----------------------------------|
| Naziv proizvoda                | Novatech                          |
| Tip                            | Tocak                             |
| Standard                       | EN12533 - Tockovi za teske terete |
| Nosivost na 4 km/h             | 3120 kg                           |
| Nosivost na 6 km/h             | 2600 kg                           |
| Električni provod              | no                                |
| nerdjajuci                     | no                                |
| Statički Nosivost              | 5200 kg                           |
| Temperaturni opseg (Minimalno) | -10 °C                            |
| Opseg temperature (maksimalni) | 60 °C                             |
| Ukupna težina                  | 18.81 kg                          |




**NOVATECH**

FTP 300x100-Ø40 HL120

EAN 4031582319439

Broj porudžbine 00801175



BETTER MOBILITY. BETTER LIFE.