

FOOTMASTER

FOOT MASTER GAPHD-075-ASF-HUD



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	200 kg
Electric Conductive	No
Stainless	No
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	115 mm
Overall width	90 mm
Overall weight	3.06 kg

HOUSING

Offset	35 mm
Swivel radius	75 mm
Swivel interference	150 mm
Dome diameter	72 mm

WHEEL

Tread Material Mix	Double flanged with tracks
Bearing	Unmachined hub
Diameter	75 mm
Tread width	23 mm
Body width	23 mm

FITTING

Plate length	100 mm
Plate width	100 mm
Plate hole length (Minimum)	78 mm
Plate hole length (Maximum)	64 mm
Plate hole width (Minimum)	78 mm
Plate hole width (Maximum)	64 mm
Plate hole diameter	10.5 mm

FOOTMASTER

FOOT MASTER GAPHD-075-ASF-HUD



BETTER MOBILITY. BETTER LIFE.

Product Drawings

