

FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225
Order number 00800107



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

HOUSING

Offset	1.46 in
Swivel radius	4.8 in
Swivel interference	9.61 in
Dome diameter	5.71 in

FITTING

Plate length	5.71 in
Plate width	5.71 in
Plate hole length (Maximum)	4.72 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.43 in

PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 1.8 mph	1388.91 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	7.87 in
Overall width	6.3 in
Overall weight	38.67 lb

WHEEL

Bearing	Unmachined hub
Diameter	5.91 in
Tread width	1.57 in
Body width	1.57 in

FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225
Order number 00800107



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

