

PRODUCT INFORMATION

DURATECH

U00160x40-Ø20 HL58

EAN 4031582442731



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Duratech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 500 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1000 kg                       |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall weight              | 0.45 kg                       |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread Material Mix    | Identical with wheel body |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 160 mm                    |
| Tread width           | 40 mm                     |
| Axle Hole Diameter    | 20 mm                     |
| Hub Length            | 58 mm                     |
| Hardness of tread (D) | 75 Shore D                |

# DURATECH

UOO160x40-Ø20 HL58

EAN 4031582442731



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

