

PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081
Broj porudžbine 00031045



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Pneumatička guma, profil bloka
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	260 mm
Širina omotac	85 mm
dimenzija rupa osovina	25 mm
dužina glavicine	74 mm
Teškoća gazećeg omotac (A)	55 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech air
Tip kućišta	Tocak
Nosivost na 3 km/h	150 kg
Statički Nosivost	150 kg
Ukupna težina	1,04 kg

PURETECH AIR

PQR260X85-Ø25 HL74 2PR

EAN 4031582321081
Broj porudžbine 00031045



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

