

PRODUCT INFORMATION

# MAXTECH

PNR400x90-Ø20 HL74 TBL

EAN 4031582411058



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.79 in
Hub length	2.91 in

### PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	319.67 lb
Electric conductive	no
Stainless	no
Load capacity Static	639.34 lb
Overall weight	6.61 lb

# MAXTECH

PNR400x90-Ø20 HL74 TBL

EAN 4031582411058



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

