

PRODUCT INFORMATION

# MAXTECH

UAR 125x32-Ø12 HL44,4

EAN 4031582323146



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing
Wheel Color	Blue grey (RAL7031)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	32 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

## CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.27 kg

# MAXTECH

UAR 125x32-Ø12 HL44,4

EAN 4031582323146

Order number 00007012  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

