

ALPHA STAINLESS

8470PJO125P30-13

EAN 4031582441765



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall weight	0.93 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	85 Shore A

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA STAINLESS

8470PJO125P30-13

EAN 4031582441765



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

