

STYLEA

5925UAP075S70 10X15 RAL9002 TFR

EAN 4031582394528



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.23 in
Overall width	2.13 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.59 in

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	0.91 in
Swivel radius	3.19 in
Swivel interference	6.38 in
Dome diameter	1.18 in
Thread diameter	0.39 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in

PRODUCT INFORMATION

STYLEA

5925UAP075S70 10X15 RAL9002 TFR

EAN 4031582394528



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

