PRODUCT INFORMATION

# ALPHA

3477POO100P30-13

EAN 4031582305500



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion resistance | ●●●○○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Alpha |
| Type | Swivel caster with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 275.58 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 551.16 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 5.04 in |
| Overall weight | 1.97 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 1.61 in |
| Swivel radius | 4.76 in |
| Swivel interference | 9.53 in |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.42 in |
| Hardness of tread (D) | 65 Shore D |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.51 in |

© Copyright 2026 TENTE International GmbH


# ALPHA


3477POO100P30-13

EAN 4031582305500

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH