

MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146
Order number 00007012



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Roller bearing |
| Wheel color | Blue gray (RAL7031) |
| Threadguards | Without threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Axle hole diameter | 0.47 in |
| Hub length | 1.75 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Maxtech |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 440.92 lb |
| Load capacity Static | 881.85 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 0.6 lb |

MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146
Order number 00007012



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

