

R47-21,5-24 INOX

EAN 4031582428292



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.28 lb

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	0.85 in
Expander fitting (Maximum)	0.94 in
Hint	Please indicate required tube innerdiameter when ordering.