

GALEA

5077PIP100R05-22X40

EAN 4031582354782



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Galea
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	139 mm
Overall weight	0.595 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	75 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Offset	40 mm
Swivel interference	205 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	22 mm
Bolt length	40 mm

GALEA

5077PIP100R05-22X40

EAN 4031582354782



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

