

# NOVATECH

ETP 082X28-Ø12 HL26

EAN 4031582318654  
Broj porudžbine 00830658

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	82 mm
Širina omotac	28 mm
dimenzija rupa osovina	12 mm
dužina glavčine	26 mm
Širina tela	28 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6201

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	350 kg
Statički Nosivost	700 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,477 kg

# NOVATECH

ETP 082X28-Ø12 HL26

EAN 4031582318654  
Broj porudžbine 00830658



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

