

NOVATECH

ITP150X50-Ø20-SH80A CONVEX

EAN 4031582329513



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Nosivost na 6 km/h	400 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C

TEHNIČKI CRTEŽI

