

DURATECH

MOP 300X80-Ø50 HL90

EAN 4031582320091

Broj porudžbine 00830851



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni ležaj
Boja Tocak	Prirodno belo
štitnici omotaca	Bez stražara
Prečnik	300 mm
Širina omotac	80 mm
dimenzija rupa osovina	50 mm
dužina glavčine	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6310

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	7800 kg
Nosivost na 6 km/h	6500 kg
Statički Nosivost	13000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	8,32 kg

DURATECH

MOP 300X80-Ø50 HL90

EAN 4031582320091

Broj porudžbine 00830851



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

