

# DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053  
Broj porudžbine 00801262

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni ležaj
Boja Tocak	Prirodno belo
štitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	35 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6307

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	3360 kg
Nosivost na 6 km/h	2800 kg
Statički Nosivost	5600 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	2,578 kg

# DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053  
Broj porudžbine 00801262



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

