

DURATECH SILENT

HUR 125X36-Ø12 HL44

EAN 4031582319644
Order number 00030828



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Damping, hybrid material
Tread material	Polyamide
Bearing	Roller bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	36 mm
Axle hole diameter	12 mm
Hub length	44 mm
Body width	36 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech silent
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.602 kg

DURATECH SILENT

HUR 125X36-Ø12 HL44

EAN 4031582319644
Order number 00030828



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

