

STYLEA

5920UOI075L51-10 DM22 RL9006

EAN 4031582310993
Order number 00074039



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	76 mm
Overall width	64 mm
Overall weight	0.122 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	10 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	White aluminium (RAL9006)
Swivel radius	60 mm
Swivel interference	120 mm
Dome diameter	22 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm

PRODUCT INFORMATION

STYLEA

5920UOI075L51-10 DM22 RL9006

EAN 4031582310993
Order number 00074039



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

