PRODUCT INFORMATION

EXPANDER

R07-Ø19-21,5 Inox_TBE

EAN 4031582437812



Image may differ from the original product

PERFORMANCE

Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Expander
Type	Accessory
Electric Conductive	No
Stainless	Yes
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall weight	0.12 kg

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	19 mm
Expander fitting (Maximum)	21.5 mm
Hint	Please indicate required tube innerdiameter when ordering.

© Copyright 2026 TENTE International GmbH