

NOVATECH

ETP 085X75-Ø20 HL75

EAN 4031582318777
Broj porudžbine 00803770

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	85 mm
Širina omotac	75 mm
dimenzija rupa osovina	20 mm
dužina glavcine	75 mm
Širina tela	75 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,251 kg

NOVATECH

ETP 085X75-Ø20 HL75

EAN 4031582318777
Broj porudžbine 00803770



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

