

DURATECH

TOP 085X85-Ø20 HL85

EAN 4031582331219

Broj porudžbine 00832615



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	85 mm
Širina omotac	85 mm
dimenzija rupa osovina	20 mm
dužina glavcine	85 mm
Širina tela	85 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	800 kg
Nosivost na 6 km/h	640 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,566 kg

DURATECH

TOP 085X85-Ø20 HL85

EAN 4031582331219
Broj porudžbine 00832615



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

