

PURETECH

PVR080X35-Ø12 HL44,4

EAN 4031582442397



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.36 lb

PURETECH

PVR080X35-Ø12 HL44,4

EAN 4031582442397



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

