



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea
Type	Swivel caster with combined lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	242.51 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	485.02 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.83 in
Overall width	3.23 in
Overall weight	2.48 lb
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Housing Color	Gray white (RAL9002)
Offset	1.57 in
Swivel radius	5.08 in
Swivel interference	10.16 in
Dome diameter	2.05 in

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Tread color	Slate gray (RAL7015)
Wheel color	Slate gray (RAL7015)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	0.79 in
Body width	0.79 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	3.74 in
Plate width	2.76 in
Plate hole length (Minimum)	1.75 in
Plate hole length (Maximum)	2.05 in
Plate hole width (Minimum)	2.83 in
Plate hole width (Maximum)	2.99 in
Plate hole diameter	0.33 in
Hint	Washable beds must be sealed in the fitting area by the hospital bed manufacturer.

LINEA

594CXSC125P50 RAL9002

Order number 00773057



BETTER MOBILITY. BETTER LIFE.

Product Drawings



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award