

# ZETA

4681SFP200P63

EAN 4031582444759



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Zeta                                |
| Type                        | Swivel castor with directional lock |
| Standard                    | EN12532 - Transport Equipment       |
| Load capacity at 4 km/h     | 600 kg                              |
| Load capacity at 6 km/h     | 500 kg                              |
| Load capacity Static        | 1200 kg                             |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 80 °C                               |
| Overall height              | 240 mm                              |
| Overall weight              | 5.236 kg                            |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Sheet steel, heavy                    |
| Tread hardness        | soft                                  |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Axle                  | Screwed with nut                      |
| Threadguards          | With threadguard                      |
| Diameter              | 200 mm                                |
| Tread width           | 50 mm                                 |
| Hardness of tread (A) | 67 Shore A                            |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Material fork       | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 55 mm                                   |
| Swivel interference | 438 mm                                  |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Maximum) | 105 mm                   |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 80 mm                    |
| Plate hole diameter         | 11 mm                    |

## TECHNICAL DRAWINGS

