

# DURATECH

UOR150X40-Ø20 TFR

EAN 4031582390698



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	150 mm
Tread width	46 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.57 kg

# DURATECH

UOR150X40-Ø20 TFR

EAN 4031582390698



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

